

Palm Grips • with axial bearing

EH 24700.



Product Description

Advantages of axial bearing:

- Double clamping force with same grip size, by reducing the surface friction.
- Protection of workpiece by a fixed locating surface.
- Little setting due to higher pre-clamping force of bolt resp. thread.

Material

Handle

- Thermoplastic PA


Inner part

- Steel, nitrided, blackened


Screw

- Steel, blackened, quality 8.8

Drawing



picture 1



picture 2

Order information

Dimensions										Art. No.
d ₁	d ₂	l +2	d ₃	h ₁ ~	h ₂ ~	t ₁ min.	t ₂	max.		
[mm]								[°C]	[g]	
with female thread – picture 1										
40	M 6	–	24	27	15.0	12.5	5.0	80	45	24700.0040
50	M 8	–	25	34	22.5	14.0	4.2	80	68	24700.0050
63	M10	–	30	41	26.5	18.0	5.4	80	109	24700.0063
80	M12	–	35	54	34.0	26.5	6.6	80	213	24700.0080
with screw – picture 2										
40	M 6	15	24	27	15.0	–	–	80	51	24700.0042
40	M 6	25	24	27	15.0	–	–	80	52	24700.0044
50	M 8	20	25	34	22.5	–	–	80	81	24700.0053
50	M 8	35	25	34	22.5	–	–	80	86	24700.0056
63	M10	30	30	41	26.5	–	–	80	136	24700.0066
63	M10	40	30	41	26.5	–	–	80	141	24700.0068
80	M12	30	35	54	34.0	–	–	80	259	24700.0083
80	M12	50	35	54	34.0	–	–	80	273	24700.0087