


BUTT HINGE LSA, LSB

SUS



● All parts made of polished stainless steel. Made to order available.

[Remarks]

● Load capacity is the value when using two hinges. For calculation conditions, please refer to INDEX 1.

RHS	CAD	Item Code	Item Name	Holes	Material	Finish	H	W	P ₁	P ₂	P ₃	P ₄	t	d	D ₁	D ₂	N ₁	Load Capacity N / 2 pcs	Load Capacity kgf / 2 pcs	Weight (g)	Box (pcs)	Carton (pcs)		
CONCEALED HINGES	3D	170-090-730	LSA-40	Without screw holes	Stainless Steel (SUS304)	Mirror	40	35					1.5		3	6.3		69	7	25	100	400		
		170-090-731	LSA-50				50										88	9	30	100	400			
		170-090-718	LSA-65				65	50					2		4.5	8.8		157	16	66	50	200		
		170-090-719	LSA-75				75										186	19	76	40	160			
BUTT HINGES	3D	170-090-734	LSA-90	Without screw holes			90	60					3		6	12.3		333	34	190	10	80		
		170-090-735	LSA-100				100									363	37	200	10	60				
		170-090-724	LSB-40				40	35	22	26			1.5	3.2	3	6.3	4	69	7	25	100	400		
		170-090-725	LSB-50				50			34							88	9	30	100	400			
PIANO HINGES	3D	170-090-716	LSB-65	With screw holes			65	50	30	23	23		2	4.3				157	16	64	50	200		
		170-090-717	LSB-75				75			27	27			5.3	4.5	8.8	6	186	19	74	40	160		
		170-090-728	LSB-90				90	60	38	35	35		3	6.4	6	12.3		333	34	180	10	80		
		170-090-729	LSB-100				100			26	26	26					8	363	37	195	10	60		

Refer to 1 : P.43


BUTT HINGE LSF

NSF SUS316



[Remarks]

● Load capacity is the value when using two hinges. For calculation conditions, please refer to INDEX 1.



No.	Part Name	Material	Finish
①	Body	Stainless Steel (SCS14)	Mirror
②	Shaft	Stainless Steel (SUS316)	-

※SCS14 is equivalent to SUS316.

RHS	CAD	Item Code	Item Name	H	W	P ₁	P ₂	P ₃	P ₄	t	D ₁	D ₂	Knuckles	N	d	Load Capacity N / 2 pcs	Load Capacity kgf / 2 pcs	Weight (g)	Box (pcs)	Carton (pcs)
CONCEALED HINGES	3D	170-090-720	LSF-50	50	50	35	15	20		5	14	6			Counterbore for M4	275	28	110	20	100
		170-090-721	LSF-65	65	65	40		35	-				3	4	Counterbore for M5	353	36	190	20	80
		170-090-722	LSF-75	75	75	50	17.5	40		6	16	8			Counterbore for M6	500	51	305	10	50
		170-090-723	LSF-100	100	100	60	20	30	30				5	6		667	68	500	10	30

Refer to 1 : P.43