

Rubber Endstop Buffers · cylindrical

EH 25150.



Product Description

To be used as an elastic end-stop, bearing foot etc.
The hardness is $55 \pm 5^\circ$ shore A. Further shore hardnesses ($40 \pm 5^\circ$ shore A and $70 \pm 5^\circ$ shore A) on request.

Material

Support washer

- Steel, zinc-plated, blue chromated
- Stainless steel 1.4301

Threaded bushing

- Steel, zinc-plated, blue chromated
- Stainless steel 1.4301

Body

- Rubber natural caoutchouc (NR), black

Screw


- Steel, zinc-plated, blue chromated
- Stainless steel 1.4301

More information

Further products

- Support Legs, Impact cushioning

Drawing



picture 1

picture 2

Order information

Dimensions						Spring rate R ~ [N/mm]	Load capacity max. [N]	Spring range ~ [mm]	Temperature range		Weight [g]	Art. No.
d ₁	l ₁	d ₂	l ₂	s	t				min.	max.		
[mm]									[°C]			
with female thread – picture 1, steel												
10	10	M 4	–	1.2	4.0	24	59	2.50	-30	80	1.7	25150.0306
15	15	M 4	–	1.4	4.0	64	241	3.75	-30	80	4.6	25150.0309
15	20	M 4	–	1.4	4.0	57	287	5.00	-30	80	5.7	25150.0310
20	15	M 6	–	2.0	5.0	77	289	3.75	-30	80	10.0	25150.0321
20	20	M 6	–	2.0	5.0	60	302	5.00	-30	80	10.0	25150.0322
20	25	M 6	–	2.0	5.0	48	297	6.25	-30	80	13.0	25150.0323
25	15	M 6	–	2.0	5.0	163	612	3.75	-30	80	14.0	25150.0326
25	20	M 6	–	2.0	5.0	112	560	5.00	-30	80	20.0	25150.0327
25	30	M 6	–	2.0	5.0	68	509	7.50	-30	80	20.0	25150.0328
30	15	M 8	–	2.0	6.5	294	934	3.75	-30	80	20.0	25150.0331
30	20	M 8	–	2.0	6.5	185	924	5.00	-30	80	30.0	25150.0332
30	30	M 8	–	2.0	6.5	117	876	7.50	-30	80	30.0	25150.0333
40	20	M 8	–	2.0	6.5	247	1235	5.00	-30	80	50.0	25150.0341
40	30	M 8	–	2.0	6.5	213	1600	7.50	-30	80	55.0	25150.0342
40	40	M 8	–	2.0	6.5	182	1820	10.00	-30	80	80.0	25150.0343
50	20	M10	–	2.0	7.0	517	2587	5.00	-30	80	80.0	25150.0351
50	30	M10	–	2.0	7.0	327	2453	7.50	-30	80	100.0	25150.0352