

# KS/KX Series

## 直通接管:KSH(標準型)

〈M5・M6時〉




〈R時〉




適用 氣壓管外徑 mm	連接螺牙 R M	型式	H (六角 對邊)	D1	D2	L	※A	M	最小 孔徑	有孔徑面積 mm <sup>2</sup>		質量 g				
										尼龍	聚氨酯					
4	M5×0.8	KSH04-M5	8	10.4	12	36.5	33	16	2.5	4.0	4.0	9				
	M6×1	KSH04-M6				37	34									
	1/8	KSH04-01S				12	37.1						34			
6	M5×0.8	KSH06-M5	8	12.8	14	37.5	33.5	17	2.5	4.0	4.0	12				
	M6×1	KSH06-M6				38	34						3	5.6	5.6	
	1/8	KSH06-01S				14	38.6						35.5	4	10.4	10.4
	1/4	KSH06-02S				42	36.5									
8	1/8	KSH08-01S	17	15.2	17	43.1	40	18.5	6	26.1	18.0	23				
	1/4	KSH08-02S				46.5	41					29				
	3/8	KSH08-03S				46.9	41.5					37				
10	1/4	KSH10-02S	22	18.5	22	53.5	48	21	7	36.3	29.5	55				
	3/8	KSH10-03S				53.9	48.5					63				
	1/2	KSH10-04S				56.6	49.5					81				
12	3/8	KSH12-03S	24	20.9	24	55.9	50.5	22	8	46.1	46.1	75				
	1/2	KSH12-04S				59.1	52					92				

※ R螺牙鎖入後的參考尺寸

〈M5・M6時〉



〈R時〉



## 直通接管:KXH(高速型)

〈M5・M6時〉




〈R時〉



適用 氣壓管外徑 mm	連接螺牙 R M	型式	H (六角 對邊)	D1	D2	L	※A	M	最小 孔徑	有孔徑面積 mm <sup>2</sup>		質量 g				
										尼龍	聚氨酯					
4	M5×0.8	KXH04-M5	8	10.4	13	38.5	35	16	2.5	4.0	4.0	11				
	M6×1	KXH04-M6				39	36									
	1/8	KXH04-01S				12	39.1						36			
6	M5×0.8	KXH06-M5	8	12.8	15.5	39.5	36	17	2.5	4.0	4.0	15				
	M6×1	KXH06-M6				40	36						3	5.6	5.6	
	1/8	KXH06-01S				14	41.1						38	4	10.4	10.4
	1/4	KXH06-02S				44.5	39									
8	1/8	KXH08-01S	17	15.2	18	45.1	42	18.5	6	26.1	18.0	28				
	1/4	KXH08-02S				48.5	43					34				
	3/8	KXH08-03S				48.9	44					42				
10	1/4	KXH10-02S	22	18.5	24.5	57.5	52	21	7	36.3	29.5	68				
	3/8	KXH10-03S				57.9	53					76				
	1/2	KXH10-04S				61.1	54					94				
12	3/8	KXH12-03S	24	20.9	27.5	58.9	54	22	8	46.1	46.1	88				
	1/2	KXH12-04S				62.1	55					105				

※ R螺牙鎖入後的參考尺寸

〈M5・M6時〉



〈R時〉

