

## 型式

異徑Y字型



同一方向降低尺寸，分支配管相互連接使用。

插入減徑型



快速接頭的尺寸變更使用。

管帽蓋



塞住不使用的配管時使用。

分歧




從母螺牙部的同一方向分支配管使用。




## 直通接頭:KGH

〈M5の場合〉



〈Rの場合〉



適用氣壓管 外徑mm	連接螺牙 M R	型式	H (六角 對邊)	註1) øD	L	※A	M	註2)有效斷面積 mm <sup>2</sup>		質量 g
								尼龍	聚氨酯	
4	M5×0.8	KGH04-M5	8	8	17	13.9	12.7	4	4	2.4
	1/8	KGH04-01	10	-	21.1	18	16	5.6	4	9
	1/4	KGH04-02	14	-	19	13.5	16	5.6	4	16
6	M5×0.8	KGH06-M5	10	10	17.8	14.7	13.5	4	4	3.4
	1/8	KGH06-01	12	-	21.6	18.5	17	13.1	10.4	16
	1/4	KGH06-02	14	-	22.5	17	17	13.1	10.4	14
	3/8	KGH06-03	17	-	20.9	15.5	17	13.1	10.4	27
8	1/8	KGH08-01	14	-	27.1	24	18.5	26.1	18.0	21
	1/4	KGH08-02	14	-	26	20.5	18.5	26.1	18.0	19
	3/8	KGH08-03	17	-	20.9	15.5	18.5	26.1	18.0	26
10	1/8	KGH10-01	17	-	29.1	26	21	26.1	26.1	19
	1/4	KGH10-02	17	-	33	27.5	21	41.5	29.5	30
	3/8	KGH10-03	17	-	27.9	22.5	21	41.5	29.5	30
	1/2	KGH10-04	22	-	26.1	19	21	41.5	29.5	53
12	1/4	KGH12-02	19	-	34	28.5	22	58.3	46.1	42
	3/8	KGH12-03	19	-	28.9	23.5	22	58.3	46.1	34
	1/2	KGH12-04	22	-	29.1	22	22	58.3	46.1	51
16	3/8	KGH16-03	24	-	38.4	32	24	81	(81)	61
	1/2	KGH16-04	24	-	34.6	26.5	24	113	(96)	47

※R螺牙鎖入後的參考尺寸

註1) øD為最大徑的意思。


註2) ( )內尺寸為軟尼龍の場合



## 附六角孔直通接頭:KGS

〈M5の場合〉

〈Rの場合〉



適用氣壓管 外徑mm	連接螺牙 M R	型式	H (六角 對邊)	註) øD	L	※A	M	有效斷面積 mm <sup>2</sup>		質量 g
								尼龍	聚氨酯	
4	M5×0.8	KGS04-M5	2.5	8	18.7	15.6	12.7	4	4	2.6
	1/8	KGS04-01	3	9.8	23	19	16	4.1	3.6	8
6	M5×0.8	KGS06-M5	2.5	10	19.5	16.4	13.5	4	4	3.2
	1/8	KGS06-01	4	11.8	24	20	17	10.0	9.9	9
	1/4	KGS06-02	4	13.8	24	18	17	10.7	10.0	15
8	1/8	KGS08-01	5	14	28	24	18.5	17.2	16.2	12
	1/4	KGS08-02	6	14	25.5	19.5	18.5	23.3	16.2	11
	3/8	KGS08-03	6	17	27.5	21.5	18.5	23.3	16.2	24
10	1/8	KGS10-01	5	17	30	26	21	17.2	10.0	18
	1/4	KGS10-02	8	17	27.5	21.5	21	39.0	26.6	12
	3/8	KGS10-03	8	17	27.5	21	21	39.0	26.6	19
	1/2	KGS10-04	22	22	28	20	21	39.0	26.6	35
12	1/4	KGS12-02	8	19	33.5	27.5	22	46.0	44.5	23
	3/8	KGS12-03	10	19	29	22.5	22	60.0	44.5	18
	1/2	KGS12-04	10	22	28	20	22	60.0	44.5	30

※R螺牙鎖入後的參考尺寸

註) øD為最大徑的意思。