


DOUBLE ACTION HINGE HG-BH




- Opens 180° in both left and right direction.

[Remarks]

● Recommended for use in pairs.

[Application Example]



RoHS	CAD	Item Code	Item Name	Material	Finish	H	W1	W2	T	P1	P2	P3	D	Door Width	Door Height	Door Weight kg/2 pcs	Weight (g)	Box (pcs)	Carton (pcs)
		170-090-065	HG-BH60	Stainless	Satin	60	64	29	5.5	13.5	4.8	47	6.5	Max. 450	Max. 700	Max. 2.6	65	20	260
		170-090-066	HG-BH70	Steel		70	78	35	7.5	22	6.8	57	7				130	10	180
		170-090-067	HG-BH80	(SUS304)		80	94	43	2	6.5	66						175	10	120

CORNER FASTENER HINGE (W/ LOCK) **STH-C64**



- Combination of hinge and corner fastener.
- Works with STF-C64A and STF-C64B fastener **1**
- Can be installed on cabinet corner.
- Locks when fastened to prevent accidental release.
- Sealing pin (sold separately) may be installed.

[Applications]



- Doors and covers required for dustproof and drip-proof.
- Doors and covers required for vibration proof.
- Measurement equipment, communication equipment, machine tools, etc.




Step 1.
After locked.

Step 2.
Pull the lever and lift the latch.

Step 3.
Release the lock of the
fastener to open the lid.



Pull the lever ✖ while pushing the lock release lever to lift the latch to open the lid.



RdHS	CAD	Item Code	Item Name	Material	Finish	Door Width	Door Height	Door Thickness	Door Weight kg/2 pcs	Weight (g)	Box (pcs)	Carton (pcs)
		170-091-430	STH-C64	Stainless Steel (SUS304)	Barrel Polished	Max. 300	Max. 400	24-28	Max. 2.8	90	10	140

Refer to **1** : P.504