

CONCEALED HINGE (CLIP-ON) HT160THV2



Passed 10,000 open/
close private cycle test

- Sheet metal door can be quickly installed and removal.
- Spacers on the slide arms reduce arm wear and door sagging.
- Door opens without interfering with side cabinets or wall.
- For more details , please contact local representatives.


[Applications]

- Small vending machines, ticket vending machines, contiguous doors, door of cabinet embedded in the wall, etc.


[Sold Separately]

- Mounting plate HT160TZ

● Outline drawing S=1/4




● Cut out dimensions



Drawing above is Bore Distance 7 mm, Door Thickness 30 mm and 15 mm Overlay.

● Locus chart



Reference door weight: 20 kg
(In case of door size W450×H800, installation pitch 550, using 2 pcs vertically)

[Hinge Body]

RHS	CAD	Item Code	Item Name	Material	Finish / Colour	Weight (g)	Box (pcs)
		160-070-327	HT160THV2-G	Body/Steel, Cup/Zinc Alloy (ZDC), Spacer/POM	Body • Cup/Nickel, Spacer/Black	204.6	100

[Mounting Plate] Sold Separately

RHS	CAD	Item Code	Item Name	Material	Finish	Weight (g)	Box (pcs)
		160-070-391	HT160TZ	Steel	Nickel	69.1	200

※ Use in combination of hinge body and mounting plate (sold separately).