

LID STAY L-195, L-270

TEST
METHOD 16

L=R


TITANIUM

SUS

L-195A-TI (Titanium alloy)

Passed 10,000 open/
close private cycle test
(for L-195 only)

L-270B (Stainless Steel)

Opening Direction	Description	Non-handed	Qty	Compression Load
 Upward-opening※	Holds When Fully Opened	Yes	1 Pc Per Door	147 N/pc (15 kgf/pc)

※Can also be used for top-opening lid, depending on installation conditions. Please confirm with actual item in detail.

- Holds the lid in fully opened position. Slightly lift up the lid to release stopper.

[Remarks]

- Appropriate bracket position can be determined depending on door height and opening angle. In this case, ensure that L_2 of the installation example is larger than L_2 shown in the figure below. (Or the hinge and stay may be damaged.)
- Use 1 pc for 1 door. If using 2 pcs, left and right operation may not be synchronised.
- Do not use this product as a stopper other than for a door.
- Allow room for stroke depending on installation location and purpose.
- Securely fix the mounting screws with screw adhesive.
- Calculate suitable door size with reference to LID STAY L SERIES 1.

[Installation] For right side board







Figure above shows L-195B or L-270B.


[Stopper Release]












Type A Case bracket



Type A Arm bracket



RHS	CAD	Item Code	Item Name	Installation hole	Material	Finish	L ₁	L ₂	L ₃	L ₄	L ₅	S	A	B	C	θ	Approx. Door Height	Compression Load N/pc	Compression Load kgf/pc	Weight (g)	Box (pcs)	Carton (pcs)
		180-100-114	L-195A	Long hole	Stainless Steel (SUS304)	Satin	195	133	148	129	121	62	90	225	86.2	66°	250-350	147	15	120	10	100
		180-100-115	L-195B	Round hole	Stainless Steel (SUS304)	Satin														124	10	100
—		180-100-118	L-195A-TI	Long hole	Titanium	Satin														71	10	100
		180-100-116	L-270A	Long hole	Stainless Steel (SUS304)	Satin														150	10	100
		180-100-117	L-270B	Round hole	Stainless Steel (SUS304)	Satin	270	170	185	166	158	100	105	275	105.8	82°	320-500			183	10	100
—		180-100-119	L-270A-TI	Long hole	Titanium	Satin														87	10	100

Refer to 1 : P.399