


[Door Size Ranges]



Refer to the left graph as a guide for model selection. When using a door with size not given here, calculate the door moment as follows. Door weight includes attached decorations.

Maximum Door Moment (N · m)
 = Door weight (kg) × 9.80665 × Distance from rotation centre to door centre of gravity (m)

When using 2 pcs per flap, the available specs will be twice.

RxHS	CAD	Item Code	Item Name	Material	Finish	Maximum Door Moment N · m/pc	Maximum Door Moment kgf · cm/pc	Recommended Thickness	Weight (kg)	Box (pcs)	Carton (pcs)
		170-034-868	LADH-35	Steel (SPCC)/	Nickel Plating/Nickel	25-35	254.9-356.9	30-50	2	1	4
		170-034-869	LADH-50		Nickel Plating/Nickel	35-50	356.9-509.9			1	4
		170-052-559	LADH-35WT	Polyacetal (POM)/ABS	Chrome/Dark Brown	25-35	254.9-356.9			1	4
		170-052-560	LADH-50WT		Chrome/Dark Brown	35-50	356.9-509.9			1	4