




TWIN WHEEL CASTER **DB, DS** Plate Type**LOAD
CAPACITY** 490 N,784 N

Drawing above shows the model with brake.

No.	Part Name	Material	Finish/Colour
①	Body	Zinc Alloy (ZDC)	Chrome
②	Plate	Steel	Clear Zinc Chromate
③	Wheel	PA	Black
④	Cover	Stainless Steel (SUS430)	—

RoHS	CAD	Item Code	Item Name	Type	D	W ₁	W ₂	H	E ₁	E ₂	Load Capacity N/pc	Load Capacity kgf/pc	Weight (g)	Box (pcs)	Carton (pcs)
✓	3D	200-132-506	DB-40P	With Brake	40.5	15	39.5	58.5	27	12.5	490	50	130	120	—
✓	3D	200-132-505	DS-40P	Without Brake	40.5	15	39.5	58.5	23.5	12.5	490	50	117	120	—
✓	3D	200-132-510	DB-50P	With Brake	50.5	18	46	71.5	33.5	17	784	80	210	100	—
✓	3D	200-132-509	DS-50P	Without Brake	50.5	18	46	71.5	29	17	784	80	196	100	—

TWIN WHEEL CASTER **DB, DS** Threaded Bolt Type**LOAD
CAPACITY** 490 N,784 N

Drawing above shows the model with brake.

No.	Part Name	Material	Finish/Colour
①	Body	Zinc Alloy (ZDC)	Chrome
②	Threaded Bolt	Steel	Metric Screw Thread: Clear Zinc Chromate Inch Screw Thread: Coloured Zinc Chromate
③	Wheel	PA	Black
④	Cover	Stainless Steel (SUS430)	—

RoHS	CAD	Item Code	Item Name	Type	D	W ₁	W ₂	H	C	d	E ₁	E ₂	Load Capacity N/pc	Load Capacity kgf/pc	Weight (g)	Box (pcs)	Carton (pcs)
✓	3D	200-133-184	DB-40-3	With Brake	40.5	15	39.5	53.5	14	W3/8	27	12.5	490	50	120	120	—
✓	3D	200-132-504	DS-40-3	Without Brake	40.5	15	39.5	53.5	14	W3/8	23.5	12.5	490	50	107	120	—
✓	3D	200-943-860	DB-40-8	With Brake	40.5	15	39.5	53.5	14	M8	27	12.5	490	50	120	120	—
✓	3D	200-943-859	DS-40-8	Without Brake	40.5	15	39.5	53.5	14	M8	23.5	12.5	490	50	107	120	—
✓	3D	200-132-502	DB-40-10	With Brake	40.5	15	39.5	53.5	14	M10	27	12.5	490	50	120	120	—
✓	3D	200-132-501	DS-40-10	Without Brake	40.5	15	39.5	53.5	14	M10	23.5	12.5	490	50	107	120	—
✓	3D	200-132-508	DB-50-3	With Brake	50.5	18	46	67.5	17	W3/8	33.5	17	784	80	204	100	—
✓	3D	200-132-507	DS-50-3	Without Brake	50.5	18	46	67.5	17	W3/8	29	17	784	80	190	100	—
✓	3D	200-943-866	DB-50-8	With Brake	50.5	18	46	67.5	17	M8	33.5	17	784	80	204	100	—
✓	3D	200-943-865	DS-50-8	Without Brake	50.5	18	46	67.5	17	M8	29	17	784	80	190	100	—
✓	3D	200-943-868	DB-50-10	With Brake	50.5	18	46	67.5	17	M10	33.5	17	784	80	204	100	—
✓	3D	200-943-867	DS-50-10	Without Brake	50.5	18	46	67.5	17	M10	29	17	784	80	190	100	—