


HOOK DS-H

TEST
METHOD 4 SUS


- Can be installed on ceilings.

[Parts Included]

- Raised countersunk head tapping screw 4×20 (SUS)

RHS	CAD	Item Code	Item Name	Material	Finish	D	H	H ₁	Load Capacity N	Load Capacity kgf	Weight (g)	Box (pcs)	Carton (pcs)
		110-020-205	DS-H-50	Stainless Steel (SUS303)	Polished	50	70	30	98	10	88	5	50
		110-020-206	DS-H-60			60	100	40					

HOOK EU

NSF TEST
METHOD 19 SUS316

- Can hang 3 items at same time.
- Two-tip shape provides stable hanging.


[Parts Included]

- EU50: Raised countersunk head wood screw 3.5×20 (SUS) (2 pcs)
- EU72: Raised countersunk head wood screw 4.1×20 (SUS) (2 pcs)

RHS	CAD	Item Code	Item Name	Material	Finish	H ₁	H ₂	W ₁	W ₂	D ₁	D ₂	D ₃	D ₄	P ₁	P ₂	d	Load Capacity N	Load Capacity kgf	Weight (g)	Box (pcs)	Carton (pcs)
		110-020-270	EU-50	Stainless Steel	Polished	50	9	22	38	38	4	17.8	5	7	20	φ4 φ7.4	196	20	42	20	120
		110-020-271	EU-72	(SCS14)		72	14	32	56	52	6	23	8	10	34	φ4.6 φ8.6	294	30	118	10	60

※SCS14 is equivalent to SUS316.

HOOK XL-HJT

TEST
METHOD 4 SUS

- Chamfered HJT 1.


[Parts Included]

- Raised countersunk head wood screw 4.1×16 (SUS)

RHS	CAD	Item Code	Item Name	Material	Finish	D	W	H	H ₁	P ₁	P ₂	Load Capacity N	Load Capacity kgf	Weight (g)	Box (pcs)	Carton (pcs)
		110-020-935	XL-HJT55M	Stainless Steel (SUS304)	Polished	33	15.5	55	23	8	19	200	20	34	30	300
		110-020-936	XL-HJT55TT		Polished and Satin Combination											
		110-020-937	XL-HJT70M		Polished	43	18.5	70	30	10	23	150	15	53	20	200
		110-020-938	XL-HJT70TT		Polished and Satin Combination											

Refer to 1 : P.726

HOOK HJT

NSF TEST
METHOD 4 SUS

- Black colour (matte) is newly launched.
- Pressing type of EL 1. (Plate thickness 4mm)

[Remarks]

- Noted that scratch is conspicuous on black surface.

[Parts Included]

- Raised countersunk head wood screw 4.1×16 (SUS)

RHS	CAD	Item Code	Item Name	Material	Finish / Colour	D	W	H	H ₁	P ₁	P ₂	Load Capacity N	Load Capacity kgf	Weight (g)	Box (pcs)	Carton (pcs)
		110-020-028	HJT-55S	Stainless Steel (SUS304)	Satin	33	15	55	23	8	19	200	20	34	30	300
		110-028-966	HJT-55SBL		Paint/Black											
		110-020-027	HJT-70S		Satin	43	18	70	30	10	23	150	15	53	20	200
		110-028-967	HJT-70SBL		Paint/Black											

Refer to 1 : P.729