


TWIN WHEEL CASTER FAU55P Plate Type



FAU55PR

FAU55PSR



Caster bracket FA55-FIX 1 to lock swivel available.

- Wheels are coated in elastomer which absorbs vibration and gives an extra smooth and quiet movement.
- With red indicator to show locked state.

[Remarks]


- Push the stopper to handle. Red lock indicator means locked state.
- The load capacities in the table below indicate the loads when moving on a smooth surface.

RHS	CAD	Item Code	Item Name	Type	Load Capacity N/pc	Load Capacity kgf/pc	Weight (g)	Box (pcs)	Carton (pcs)
		200-133-278	FAU55PSR	With Brake	686	70	179	4	72
		200-133-283	FAU55PR	Without Brake			175	4	72

Refer to 1 : P.903

LOAD CAPACITY 686 N

Drawing below shows the model with brake.



No.	Part Name	Material	Finish/Colour
①	Body	Aluminium Alloy (ADC)	Silver Enamel Finish
②	Plate	Steel (SPCC)	Coloured Zinc Chromate
③	Wheel	PA + Elastomer (TPU)	Black
④	Cover	PA	
⑤	Bush		
⑥	Stopper		Black + Red

TWIN WHEEL CASTER FAU55N Threaded Bolt Type

LOAD CAPACITY 686 N













FAU55N3R

FAU55N3SR

- Wheels are coated in elastomer which absorbs vibration and gives an extra smooth and quiet movement.
- With red indicator to show locked state.


[Remarks]

- Push the stopper to handle. Red lock indicator means locked state.
- The load capacities in the table below indicate the loads when moving on a smooth surface.
- The threaded bolt has a dished dent at the upper end for N10 only.

RHS	CAD	Item Code	Item Name	Type	d	Load Capacity N/pc	Load Capacity kgf/pc	Weight (g)	Box (pcs)	Carton (pcs)	
		200-133-279	☆FAU55N3SR	With Brake	W3/8	686	70	155	4	72	
		200-133-284	☆FAU55N3R	Without Brake					151	4	72
		200-133-280	FAU55N10SR	With Brake	M10				155	4	72
		200-133-285	FAU55N10R	Without Brake					151	4	72
—		200-133-281	☆FAU55N12SR	With Brake	M12				155	4	72
		200-133-286	☆FAU55N12R	Without Brake					151	4	72

☆Limited stock available. Please contact your local agent or your nearest Sugatsune subsidiary for detail/availability.

Drawing below shows the model with brake.



No.	Part Name	Material	Finish/Colour
①	Body	Aluminium Alloy (ADC)	Silver Enamel Finish
②	Threaded Bolt	Steel (SWCH)	Coloured Zinc Chromate
③	Wheel	PA + Elastomer (TPU)	Black
④	Cover	PA	
⑤	Bush		
⑥	Stopper		Black + Red


TWIN WHEEL CASTER FAU55S Insert Bolt Type

LOAD CAPACITY 686 N



FAU55SR

FAU55SSR



- Wheels are coated in elastomer which absorbs vibration and gives an extra smooth and quiet movement.
- With red indicator to show locked state.

[Remarks]

- Push the stopper to handle. Red lock indicator means locked state.
- The load capacities in the table below indicate the loads when moving on a smooth surface.


[Parts Included]

- Socket

RHS	CAD	Item Code	Item Name	Type	Load Capacity N/pc	Load Capacity kgf/pc	Weight (g)	Box (pcs)	Carton (pcs)
		200-130-909	FAU55SSR	With Brake	686	70	158	4	72
		200-130-910	FAU55SR	Without Brake			154	4	72

※Limited stock available. Please contact your local agent or your nearest Sugatsune subsidiary for detail/availability.

Drawing below shows the model with brake.



No.	Part Name	Material	Finish/Colour
①	Body	Aluminium Alloy (ADC)	Silver Enamel Finish
②	Plate	Steel (SWCH)	Coloured Zinc Chromate
③	Wheel	PA + Elastomer (TPU)	Black
④	Cover	PA	
⑤	Bush		
⑥	Stopper		Black + Red
⑦	Socket	Steel (STKM)	Coloured Zinc Chromate